

Model 2500 Mini OTR

T004

OPERATION

1. ATTACH MOLD'S TO EACH HEAT UNIT.
2. ADJUST PIVOTING FRAME FOR VERTICAL OR HORIZONTAL.
3. TURN EXTENSION TUBE 90* FOR WORK HEIGHT ADJUSTMENT.
4. RETURN TUBES TO LOCKED POSITION (NOTCHES FACE THE FRAME) SEE MANUAL.
5. CLAMP ONTO PIECE TO BE REPAIRED WITH SCREW HANDLE ON EXTENSION TUBE.
6. TURN TIMER ON TO ACTIVATE AIR BAG AND HEATERS. SET DESIRED ON OFF WITH DIGITAL READOUT MAX 360* (SEE ATTACHED MANUEL) SET AIR PRESSURE.

SPECS:

120 VOLT AMP

2 - 6" X 8" 12000 WATT HEAT UNITS

THERMOCOUPLE WITH READOUT CONTROL

MOBILE CART

5 HOUR TIMER

RAPID EXTENSION TUBE ADJUSTMENT

ADJUSTABLE WORK HEIGHT